SIEMENS

Long Life recirculation kit LZ10AFS00



- ✓ For recirculation operation✓ Including a deflector, multiple regenerative active carbon filters (2 units), flexible tube and mounting material
- ✓ Can be used multiple times, the regenerative active carbon filter is regenerated in the oven with a recommendation of every 4 months. Simply place in the oven for 2 hours at 200°C.

Technical Data

Dimensions of the packed product (HxWxD): ... 455 x 335 x 690 mm





Long Life recirculation kit LZ10AFS00

Optional accessories • For recirculation operation • Including a deflector, multiple regenerative active carbon filters (2 units), flexible tube and mounting material • Can be used multiple times, the regenerative active carbon filter is regenerated in the oven with a recommendation of every 4 months. Simply place in the oven for 2 hours at 200°C.