### **SIEMENS**

## Long Life recirculation kit LZ10AKR00



- ✓ LZ10AKR00
- ✓ Long Life recirculation kit (chimless)
- ✓ For recirculation operation
- ✓ Including multiple regenerative active carbon filters (2 units) and a diffusor for chimless operation
- ✓ Can be used multiple times, the regenerative active carbon filter
  is regenerated in the oven with a recommendation of every 4
  months. Simply place in the oven for 2 hours at 200°C.

#### Features

#### **Technical Data**



## **SIEMENS**

# Long Life recirculation kit LZ10AKR00

# • LZ10AKR00 • Long Life recirculation kit (chimless)

- **Optional accessories**
- For recirculation operation
- Including multiple regenerative active carbon filters (2 units) and a diffusor for chimless operation
- Can be used multiple times, the regenerative active carbon filter is regenerated in the oven with a recommendation of every 4 months. Simply place in the oven for 2 hours at 200°C.