


iQ700, Table induction aspirante, 80 cm, avec cadre EX875LX67E



Accessoires intégrés

1 x Connecteur télescopique mode recyclage, 1 x Filtre à charbon Clean Air Plus

Accessoires en option

HZ32WA00 Sonde à viande sans fil, HZ39050 Capteur de cuisson, HZ390522 GRIL FONTE 40X20 CM, HZ9CF240 POÊLE À FRIRE 24CM Ø, HZ9CF280 POÊLE À FRIRE 28CM Ø, HZ9FF010 PLAT A ROTIR POUR TABLE INDUCTION, HZ9FF030 SET DE RECIPIENTS PR INDUCTION 3PCS, HZ9FF040 SET DE RECIPIENTS PR INDUCTION 4PCS, HZ9SE030 Set de 2 casseroles et 1 poêle à frire, HZ9SE040 BATTERIE CUISINE 4 PCS, HZ9SE060 6 pieces Set, HZ9TY010 Teppan Yaki, HZ9VDKR2 Kit de recirculation 1x coude L, HZ9VDSB1 COUDE HORIZONTAL PLAT 90°, HZ9VDSB2 COUDE VERTICAL L 90°, HZ9VDSB4 COUDE VERTICAL S 90°, HZ9VDSIO ADAPTATEUR GAINÉ ROND/PLAT, HZ9VDSI1 Adaptateur de conduit rond-plat 90°, HZ9VDSM1 GAINÉ PLATE 500MM, HZ9VDSM2 GAINÉ PLATE 100 CM, HZ9VDSM3 GAINÉ PLATE 150MM, HZ9VDSM4 GAINÉ PLATE 200MM, HZ9VDSM5 GAINÉ PLATE 250MM, HZ9VDSM6 GAINÉ PLATE 300MM, HZ9VDSM7 GAINÉ PLATE 350MM, HZ9VDSM8 GAINÉ PLATE 400MM, HZ9VDSM9 GAINÉ PLATE 450MM, HZ9VDSM10 GAINÉ PLATE 500MM, HZ9VDSM11 GAINÉ PLATE 550MM, HZ9VDSM12 GAINÉ PLATE 600MM, HZ9VDSM13 GAINÉ PLATE 650MM, HZ9VDSM14 GAINÉ PLATE 700MM, HZ9VDSM15 GAINÉ PLATE 750MM, HZ9VDSM16 GAINÉ PLATE 800MM, HZ9VDSM17 GAINÉ PLATE 850MM, HZ9VDSM18 GAINÉ PLATE 900MM, HZ9VDSM19 GAINÉ PLATE 950MM, HZ9VDSM20 GAINÉ PLATE 1000MM, HZ9VDSM21 GAINÉ PLATE 1050MM, HZ9VDSM22 GAINÉ PLATE 1100MM, HZ9VDSM23 GAINÉ PLATE 1150MM, HZ9VDSM24 GAINÉ PLATE 1200MM, HZ9VDSM25 GAINÉ PLATE 1250MM, HZ9VDSM26 GAINÉ PLATE 1300MM, HZ9VDSM27 GAINÉ PLATE 1350MM, HZ9VDSM28 GAINÉ PLATE 1400MM, HZ9VDSM29 GAINÉ PLATE 1450MM, HZ9VDSM30 GAINÉ PLATE 1500MM, HZ9VDSM31 GAINÉ PLATE 1550MM, HZ9VDSM32 GAINÉ PLATE 1600MM, HZ9VDSM33 GAINÉ PLATE 1650MM, HZ9VDSM34 GAINÉ PLATE 1700MM, HZ9VDSM35 GAINÉ PLATE 1750MM, HZ9VDSM36 GAINÉ PLATE 1800MM, HZ9VDSM37 GAINÉ PLATE 1850MM, HZ9VDSM38 GAINÉ PLATE 1900MM, HZ9VDSM39 GAINÉ PLATE 1950MM, HZ9VDSM40 GAINÉ PLATE 2000MM, HZ9VDSM41 GAINÉ PLATE 2050MM, HZ9VDSM42 GAINÉ PLATE 2100MM, HZ9VDSM43 GAINÉ PLATE 2150MM, HZ9VDSM44 GAINÉ PLATE 2200MM, HZ9VDSM45 GAINÉ PLATE 2250MM, HZ9VDSM46 GAINÉ PLATE 2300MM, HZ9VDSM47 GAINÉ PLATE 2350MM, HZ9VDSM48 GAINÉ PLATE 2400MM, HZ9VDSM49 GAINÉ PLATE 2450MM, HZ9VDSM50 GAINÉ PLATE 2500MM, HZ9VDSM51 GAINÉ PLATE 2550MM, HZ9VDSM52 GAINÉ PLATE 2600MM, HZ9VDSM53 GAINÉ PLATE 2650MM, HZ9VDSM54 GAINÉ PLATE 2700MM, HZ9VDSM55 GAINÉ PLATE 2750MM, HZ9VDSM56 GAINÉ PLATE 2800MM, HZ9VDSM57 GAINÉ PLATE 2850MM, HZ9VDSM58 GAINÉ PLATE 2900MM, HZ9VDSM59 GAINÉ PLATE 2950MM, HZ9VDSM60 GAINÉ PLATE 3000MM, HZ9VDSM61 GAINÉ PLATE 3050MM, HZ9VDSM62 GAINÉ PLATE 3100MM, HZ9VDSM63 GAINÉ PLATE 3150MM, HZ9VDSM64 GAINÉ PLATE 3200MM, HZ9VDSM65 GAINÉ PLATE 3250MM, HZ9VDSM66 GAINÉ PLATE 3300MM, HZ9VDSM67 GAINÉ PLATE 3350MM, HZ9VDSM68 GAINÉ PLATE 3400MM, HZ9VDSM69 GAINÉ PLATE 3450MM, HZ9VDSM70 GAINÉ PLATE 3500MM, HZ9VDSM71 GAINÉ PLATE 3550MM, HZ9VDSM72 GAINÉ PLATE 3600MM, HZ9VDSM73 GAINÉ PLATE 3650MM, HZ9VDSM74 GAINÉ PLATE 3700MM, HZ9VDSM75 GAINÉ PLATE 3750MM, HZ9VDSM76 GAINÉ PLATE 3800MM, HZ9VDSM77 GAINÉ PLATE 3850MM, HZ9VDSM78 GAINÉ PLATE 3900MM, HZ9VDSM79 GAINÉ PLATE 3950MM, HZ9VDSM80 GAINÉ PLATE 4000MM, HZ9VDSM81 GAINÉ PLATE 4050MM, HZ9VDSM82 GAINÉ PLATE 4100MM, HZ9VDSM83 GAINÉ PLATE 4150MM, HZ9VDSM84 GAINÉ PLATE 4200MM, HZ9VDSM85 GAINÉ PLATE 4250MM, HZ9VDSM86 GAINÉ PLATE 4300MM, HZ9VDSM87 GAINÉ PLATE 4350MM, HZ9VDSM88 GAINÉ PLATE 4400MM, HZ9VDSM89 GAINÉ PLATE 4450MM, HZ9VDSM90 GAINÉ PLATE 4500MM, HZ9VDSM91 GAINÉ PLATE 4550MM, HZ9VDSM92 GAINÉ PLATE 4600MM, HZ9VDSM93 GAINÉ PLATE 4650MM, HZ9VDSM94 GAINÉ PLATE 4700MM, HZ9VDSM95 GAINÉ PLATE 4750MM, HZ9VDSM96 GAINÉ PLATE 4800MM, HZ9VDSM97 GAINÉ PLATE 4850MM, HZ9VDSM98 GAINÉ PLATE 4900MM, HZ9VDSM99 GAINÉ PLATE 4950MM, HZ9VDSM100 GAINÉ PLATE 5000MM, HZ9VDSM101 GAINÉ PLATE 5050MM, HZ9VDSM102 GAINÉ PLATE 5100MM, HZ9VDSM103 GAINÉ PLATE 5150MM, HZ9VDSM104 GAINÉ PLATE 5200MM, HZ9VDSM105 GAINÉ PLATE 5250MM, HZ9VDSM106 GAINÉ PLATE 5300MM, HZ9VDSM107 GAINÉ PLATE 5350MM, HZ9VDSM108 GAINÉ PLATE 5400MM, HZ9VDSM109 GAINÉ PLATE 5450MM, HZ9VDSM110 GAINÉ PLATE 5500MM, HZ9VDSM111 GAINÉ PLATE 5550MM, HZ9VDSM112 GAINÉ PLATE 5600MM, HZ9VDSM113 GAINÉ PLATE 5650MM, HZ9VDSM114 GAINÉ PLATE 5700MM, HZ9VDSM115 GAINÉ PLATE 5750MM, HZ9VDSM116 GAINÉ PLATE 5800MM, HZ9VDSM117 GAINÉ PLATE 5850MM, HZ9VDSM118 GAINÉ PLATE 5900MM, HZ9VDSM119 GAINÉ PLATE 5950MM, HZ9VDSM120 GAINÉ PLATE 6000MM, HZ9VDSM121 GAINÉ PLATE 6050MM, HZ9VDSM122 GAINÉ PLATE 6100MM, HZ9VDSM123 GAINÉ PLATE 6150MM, HZ9VDSM124 GAINÉ PLATE 6200MM, HZ9VDSM125 GAINÉ PLATE 6250MM, HZ9VDSM126 GAINÉ PLATE 6300MM, HZ9VDSM127 GAINÉ PLATE 6350MM, HZ9VDSM128 GAINÉ PLATE 6400MM, HZ9VDSM129 GAINÉ PLATE 6450MM, HZ9VDSM130 GAINÉ PLATE 6500MM, HZ9VDSM131 GAINÉ PLATE 6550MM, HZ9VDSM132 GAINÉ PLATE 6600MM, HZ9VDSM133 GAINÉ PLATE 6650MM, HZ9VDSM134 GAINÉ PLATE 6700MM, HZ9VDSM135 GAINÉ PLATE 6750MM, HZ9VDSM136 GAINÉ PLATE 6800MM, HZ9VDSM137 GAINÉ PLATE 6850MM, HZ9VDSM138 GAINÉ PLATE 6900MM, HZ9VDSM139 GAINÉ PLATE 6950MM, HZ9VDSM140 GAINÉ PLATE 7000MM, HZ9VDSM141 GAINÉ PLATE 7050MM, HZ9VDSM142 GAINÉ PLATE 7100MM, HZ9VDSM143 GAINÉ PLATE 7150MM, HZ9VDSM144 GAINÉ PLATE 7200MM, HZ9VDSM145 GAINÉ PLATE 7250MM, HZ9VDSM146 GAINÉ PLATE 7300MM, HZ9VDSM147 GAINÉ PLATE 7350MM, HZ9VDSM148 GAINÉ PLATE 7400MM, HZ9VDSM149 GAINÉ PLATE 7450MM, HZ9VDSM150 GAINÉ PLATE 7500MM, HZ9VDSM151 GAINÉ PLATE 7550MM, HZ9VDSM152 GAINÉ PLATE 7600MM, HZ9VDSM153 GAINÉ PLATE 7650MM, HZ9VDSM154 GAINÉ PLATE 7700MM, HZ9VDSM155 GAINÉ PLATE 7750MM, HZ9VDSM156 GAINÉ PLATE 7800MM, HZ9VDSM157 GAINÉ PLATE 7850MM, HZ9VDSM158 GAINÉ PLATE 7900MM, HZ9VDSM159 GAINÉ PLATE 7950MM, HZ9VDSM160 GAINÉ PLATE 8000MM, HZ9VDSM161 GAINÉ PLATE 8050MM, HZ9VDSM162 GAINÉ PLATE 8100MM, HZ9VDSM163 GAINÉ PLATE 8150MM, HZ9VDSM164 GAINÉ PLATE 8200MM, HZ9VDSM165 GAINÉ PLATE 8250MM, HZ9VDSM166 GAINÉ PLATE 8300MM, HZ9VDSM167 GAINÉ PLATE 8350MM, HZ9VDSM168 GAINÉ PLATE 8400MM, HZ9VDSM169 GAINÉ PLATE 8450MM, HZ9VDSM170 GAINÉ PLATE 8500MM, HZ9VDSM171 GAINÉ PLATE 8550MM, HZ9VDSM172 GAINÉ PLATE 8600MM, HZ9VDSM173 GAINÉ PLATE 8650MM, HZ9VDSM174 GAINÉ PLATE 8700MM, HZ9VDSM175 GAINÉ PLATE 8750MM, HZ9VDSM176 GAINÉ PLATE 8800MM, HZ9VDSM177 GAINÉ PLATE 8850MM, HZ9VDSM178 GAINÉ PLATE 8900MM, HZ9VDSM179 GAINÉ PLATE 8950MM, HZ9VDSM180 GAINÉ PLATE 9000MM, HZ9VDSM181 GAINÉ PLATE 9050MM, HZ9VDSM182 GAINÉ PLATE 9100MM, HZ9VDSM183 GAINÉ PLATE 9150MM, HZ9VDSM184 GAINÉ PLATE 9200MM, HZ9VDSM185 GAINÉ PLATE 9250MM, HZ9VDSM186 GAINÉ PLATE 9300MM, HZ9VDSM187 GAINÉ PLATE 9350MM, HZ9VDSM188 GAINÉ PLATE 9400MM, HZ9VDSM189 GAINÉ PLATE 9450MM, HZ9VDSM190 GAINÉ PLATE 9500MM, HZ9VDSM191 GAINÉ PLATE 9550MM, HZ9VDSM192 GAINÉ PLATE 9600MM, HZ9VDSM193 GAINÉ PLATE 9650MM, HZ9VDSM194 GAINÉ PLATE 9700MM, HZ9VDSM195 GAINÉ PLATE 9750MM, HZ9VDSM196 GAINÉ PLATE 9800MM, HZ9VDSM197 GAINÉ PLATE 9850MM, HZ9VDSM198 GAINÉ PLATE 9900MM, HZ9VDSM199 GAINÉ PLATE 9950MM, HZ9VDSM200 GAINÉ PLATE 10000MM

- ✓ flexInduction : la zone de cuisson intelligente qui s'adapte à la taille de vos casseroles.
- ✓ Bandeau dual lightSlider : contrôlez la cuisson du bout des doigts.
- ✓ Home Connect : obtenez des informations sur votre table de cuisson où que vous soyez via tablette ou smartphone.
- ✓ cookingSensor Plus ready : possibilité d'ajouter en option un capteur de température pour les liquides et ainsi éviter les débordements.
- ✓ powerMove Plus permet un contrôle intuitif grâce à trois zones de cuisson prédéfinies avec des températures différentes.

Équipement



Données techniques

Appellation produit/famille: Foyer en vitrocéramique
 Design: Encastrable
 Type d'énergie: Électrique
 Nombre de foyers: 4
 Niche d'encastrement: 223 x 750-750 x 490-490 mm
 Largeur: 812 mm
 Dimensions appareil H x L x P: 223x812x520 mm
 Dimensions du produit emballé: 430x950x660 mm
 Poids net: 28.9 kg
 Poids brut: 33.6 kg
 Témoin de chaleur résiduelle: Indépendant
 Emplacement du bandeau de commande: Devant
 Matériau de la surface: Vitrocéramique
 Couleur de la surface: Noir, Acier inox
 Couleur du cadre: Acier inox
 Longueur du cordon électrique: 110 cm
 Brûleurs: non
 powerBoost: Toutes les zones de cuisson
 Puissance du 2nd foyer: 3300.0 W
 Nombre de vitesses: 17 vitesses + 2 intensives
 Débit d'aspiration max. en évacuation: 500 m³/h
 Débit de l'aspiration en Recyclage d'air position turbo: 595.0 m³/h
 Débit d'aspiration max. en recyclage: 499 m³/h
 Débit d'air position intensive en évacuation: 622 m³/h
 Niveau Sonore: 69 dB(A) re 1pW
 Filtre anti-odeurs: non
 Mode d'aspiration: Recyclage ou évacuation
 Indicateur de changement de filtre: Oui
 Tension: 220-240/380-415 V
 Fréquence: 50-60 Hz
 Accessoires inclus: 1 x Connecteur télescopique mode recyclage, 1 x Filtre à charbon Clean Air Plus





iQ700, Table induction aspirante, 80 cm, avec cadre EX875LX67E

Cotes



- A:** Profondeur de dégagement
- B:** Découpe dans le panneau arrière nécessaire pour la tuyauterie. La taille et la position exactes peuvent être obtenues sur le dessin spécifique.
- C:** Tous les modèles de la classe de largeur 80 cm peuvent être installés dans des meubles de 60 cm de large en ajustant les panneaux latéraux.



- A:** Longueur de tube
- B:** Hauteur de la cuisine
- C:** Coude en S à 90°
- D:** Coude en L à 90°
- E:** Manchon de raccordement
- F:** Diffuseur
- G:** Tiroir raccourci


Kit de canalisation disponible pour les plans de travail de profondeur ≥ 600 mm et jusqu'à 960 mm de hauteur

L'installateur doit sélectionner la longueur du tube et si nécessaire le couper en fonction de la hauteur de la cuisine


A	B
500	≤ 990
1000	> 990

Cotes


mesures en mm




mesures en mm





mesures en mm





mesures en mm




mesures en mm



Cotes




Mesures en mm
 Vue de face



A: Connecté directement à l'arrière


Mesures en mm
 Vue de face - découpe du meuble pour circulation d'air sans conduit



Cotes

Mesures en mm

Vue latérale



En cas d'installation directement contre des murs extérieurs qui ne sont pas isolés ($\mu \geq 0,5 \text{ W/m}^2\text{°C}$), nous recommandons d'utiliser des configurations de recyclage partiellement ou totalement gainées.

Mesures en mm

Vue avant

